

Artículo/Article	<b>MICROFIBRA 86 TECNOSANI</b>	<b>MASK FFP2 (test itel CE-11343)</b>
REUSABLE (>25 washes)	MADE IN SPAIN	TESTED (ACCORDING UNE-EN14683 and UNE-0065 <b>CEE/93/42</b> )

### ANÁLISIS FÍSICO / PHYSICAL ANALYSIS

CARACTERÍSTICAS	RESULTADOS / RESULTS		VALORES / VALUES	TEST		
Nº de Hilo/Thread Count	Urdimbre / Warp	75D				
	Trama / Weft	150D				
Densidad / Density	Urdimbre / Warp	104				
	Trama / Weft	71				
Ligamento / Weave	PLANA / PLAIN					
Comp. Urd./ Comp. Warp	100% PES			ISO 1833:2006		
Comp. Tr./ Comp.Weft	100% PES					
Total Comp.	100% PES		Simple: No tolerancia Compuesta: +/- 3%			
Ancho Final / Final Width	cm	160 - 165	<b>+/-2%</b>	ISO 3932:1976		
Peso / Weight	gr/m <sup>2</sup>	82 - 86	<b>+/-5%</b>	ISO 3801:1977		
Resistencia Rotura/ Breakage	(Kgs.)	Urdimbre	pass	kgf	EN-13795	
		Trama	pass	kgf		
Resistencia Abrasion	pass			EN-13795		
Resistencia Desgarro / Tear	Urdimbre/Warp (G)	N/A	Trama / Weft	N/A	EN-13795	
Encogimiento / Shrinkage	°C	60	% Urdimbre	+/- 2	<b>0 - 3 %</b>	NP EN ISO 5077:2008
			% Trama	+/- 2		

### SPECIAL MEDICAL TESTS

CARACTERÍSTICAS	RESULTADOS / RESULTS		VALORES / VALUES	TEST
Washing solidity 60°C	4,5		<b>0-5</b>	UNE EN ISO-05
Pilling	5		<b>0-5</b>	UNE EN ISO 12945-2
Traspirability	< 60 Pa/cm <sup>2</sup>			AST1
Aerosol Filtration Efficiency	>95%			UNE EN14683
Particle Filtration Efficiency	>94%			UNE EN14683
Particle Filtration	0,3 micras and >95% efficiency			UNE EN149
Bacterial presence	DRY: PASS	WET: PASS		EN-13795

### ANÁLISIS QUÍMICO / CHEMICAL ANALYSIS

CARACTERÍSTICAS	RESULTADOS / RESULTS		VALORES / VALUES	TEST
pH	Conforme/According Oeko-Tex II		4,0 - 7,5	UNI EN ISO 3071/06
Formaldehído	Conforme/According Oeko-Tex II		<16ppm   <b>&lt;75ppm</b>	UNE EN ISO 14184-1:1999
Arlaminas	Conforme/According Oeko-Tex II		<b>20 ppm</b>	UNE 2002/61/CE

### PROHIBIDOS / FORBIDDEN

Metales Pesados	Conforme/According Oeko-Tex II	Niquel 0,5 Pg/cm <sup>2</sup> - Cadmio 75 pm - Plomo 100 ppm
AZO Colorants	Conforme/According Oeko-Tex II	No detectable
Colorantes Alérgicos	Conforme/According Oeko-Tex II	No detectable (LMBG) (1/4/96)

#### SÍMBOLOS DE LAVADO / WASH CARE SYMBOLS



#### Observaciones:

**TRAS 25 LAVADOS EL ACABADO EMPIEZA A PERDER PROPIEDADES - LAVAR CON DETERGENTE NEUTRO**

*AFTER 25 WASHES THE FINISH BEGINS TO LOSE PROPERTIES - WASH WITH NEUTRAL DETERGENT*

**NO USAR LEJIA / DO NOT USE BLEACHING**

**PLANCHADO A 140° de 10-15 SEGUNDOS / IRON 140° FOR 10-15 SECONDS**

**GRS POST CONSUME bajo pedido / on request**